


ARCHITECTURAL SPECIFICATIONS:

Heavy Duty Shower Bench - CA420-SD



OPERATION:

Seat is automatically held in a raised position by a stainless cross member attached to the front and rear support legs. When seat is lowered into the down position, the swing down leg automatically aligns the front and rear support legs with the help of the stainless cross member.

FRAME: Type 304 (18-8) S.S. tube, 1-1/4" (32 mm) x 18ga. (1.2mm) sq. mainframe with 1" (25mm) x 18ga. (1.2mm) rd. cross members . Leg: "H"-shaped yoke of type 304 (18-8) S.S. tubing, 1" (25mm) x 18ga. (1.2mm) rd. tubing, Heliarc welded to 1-1/4" (32mm) rd. x 12ga. (2.7mm) frame hinge. The swing down legs automatically level when the seat is lowered to a horizontal sitting position. The seat automatically locks itself when raised into its "up" position with the use of the stainless cross member.

WALL FLANGES (2): Type 304 (18-8) SS, 10ga. (3.4mm) x 3" (76mm) dia. Heliarc welded to 1" (25mm) rd. x 18ga. (1.2mm) 90 degree leg supports, and to 1-1/4" (32mm) rd. x 12ga. (1.7mm) frame hinge couplings. Three mounting holes in each flange.

SWING DOWN LEGS: "H" shaped yoke of type 304 (18-8) SS 1" dia. (25mm) x 18ga. (1.2mm) rd. tubing , heliarc welded to 1-1/4" (32mm) rd. x 12ga. (2.7mm) frame hinge couplings.

SEAT CHOICES (Designate when ordering)

PW or PT or PA - White (PW) or Teak (PT) or Almond (PA) finish
Phenolic 1/2" (13mm) x 3" (76mm) slats bolted to frame with SS screws.

INSTALLATION:

All Shower Seats must only be installed using suitable fasteners and sufficient in-wall backing materials. ADA mounting height for seat in lowered position is 17" (432mm) to 19" (482m)

MJC Designs, LLC
Compliance Alliance
77 Zion Park Ct
Troy, VA 22974